

**Garant**

**Carbide quick-change boring bar E.. SDUCR 93°, for indexable inserts DC., right-hand, Shank  $\varnothing$  DS / insert size: 8/04mm**


**Order data**

Order number	268114 8/04
GTIN	4062406584009
Item class	21P

**Technical description**

Head length $L_1$	26 mm
ISO code toolholder	E08X SDUCR/L04
Shank $\varnothing$ $D_s$	8 mm
Setting angle $\kappa$	93 degrees
Pack of insert screws	269028 26
Minimum pre-drill $\varnothing$ $D_{min}$	5.6 mm
Neck width $L_4$	4 mm
suitable indexable insert	DC.. 04T0..
Usable depth T	1.5 mm
Overall length L	57 mm
Centre offset $L_3$	3 mm
Insert size	4 mm
Standard	Works standard
Application type	right-hand
Tool material	Carbide
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar