

Garant

**Carbide boring bar E.. SVVCL 72,5°, for indexable inserts VC.., left-hand,
Shank Ø / insert size: 10/07mm**


Order data

Order number	261337 10/07
GTIN	4062406285579
Item class	21T

Technical description

Minimum pre-drill $\varnothing D_{\min}$	12.5 mm
Overall length L	100 mm
Head length L_1	32 mm
Neck width L_4	6.8 mm
Centre offset L_3	8 mm
Insert size	7 mm
Pack of insert screws	269028 26
Clamping height L_2	9 mm
ISO code toolholder	E10H SVVCR/L07
Setting angle κ	72.5 degrees
suitable indexable insert	VC.. 0702..
Usable depth T	6 mm
Shank $\varnothing D_s$	10 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	8xD

Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 27	269028 27
------------------------------	-----------