

**Garant**

**Carbide quick-change boring bar E.. SVJCR 142°, for indexable inserts VC.., right-hand, Shank dia. DS / insert size: 8/05mm**


**Order data**

Order number	268116 8/05
GTIN	4062406584122
Item class	21P

**Technical description**

Head length $L_1$	26 mm
Pack of insert screws	269028 26
ISO code toolholder	E08X SVJCR/L05
Setting angle $\kappa$	142 degrees
Centre offset $L_3$	2 mm
suitable indexable insert	VC.. 0501..
Neck width $L_4$	4 mm
Minimum pre-drill $\varnothing D_{min}$	5.5 mm
Overall length L	57 mm
Shank $\varnothing D_s$	8 mm
Standard	Works standard
Application type	right-hand
Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

---

## Accessories

Set of insert screws Type 26

269028 26