

Garant

Carbide quick-change boring bar E.. SVJCL 142°, for indexable inserts VC.., left-hand, Shank dia. DS / insert size: 8/05mm


Order data

Order number	268117 8/05
GTIN	4062406584139
Item class	21P

Technical description

Minimum pre-drill $\varnothing D_{\min}$	5.5 mm
Setting angle κ	142 degrees
Centre offset L_3	2 mm
Shank $\varnothing D_s$	8 mm
Overall length L	57 mm
suitable indexable insert	VC.. 0501..
Pack of insert screws	269028 26
Head length L_1	26 mm
ISO code toolholder	E08X SVJCR/L05
Neck width L_4	4 mm
Standard	Works standard
Application type	left-hand
Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 26

269028 26