

Garant

Carbide quick-change boring bar E.. SVLCR 95°, for indexable inserts VC., right-hand, Shank dia. DS / insert size: 8/05mm


Order data

Order number	268120 8/05
GTIN	4062406584160
Item class	21P

Technical description

suitable indexable insert	VC.. 0501..
Overall length L	57 mm
ISO code toolholder	E08X SVLCR/L05
Minimum pre-drill $\varnothing D_{\min}$	9.2 mm
Pack of insert screws	269028 26
Setting angle κ	95 degrees
Centre offset L_3	5 mm
Head length L_1	26 mm
Usable depth T	3 mm
Neck width L_4	6 mm
Shank $\varnothing D_s$	8 mm
Insert size	5 mm
Standard	Works standard
Application type	right-hand
Tool material	Carbide
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 26	269028 26
------------------------------	-----------