

**Garant**

**Carbide boring bar E.. SV95CR 95°, for indexable inserts VC., right-hand,  
Shank Ø / insert size: 16/07mm**


**Order data**

Order number	261342 16/07
GTIN	4062406285630
Item class	21T

**Technical description**

Overall length L	150 mm
Centre offset L <sub>3</sub>	11 mm
Neck width L <sub>4</sub>	12.9 mm
ISO code toolholder	E16M SV95CR/L07
Insert size	7 mm
Clamping height L <sub>2</sub>	15 mm
Minimum pre-drill Ø D <sub>min</sub>	19.5 mm
Pack of insert screws	269028 26
Setting angle κ	95 degrees
suitable indexable insert	VC.. 0702..
Head length L <sub>1</sub>	55 mm
Usable depth T	8 mm
Shank Ø D <sub>s</sub>	16 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	8×D

Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

---

## Accessories

Set of insert screws Type 27	269028 27
------------------------------	-----------