

Garant

Carbide quick-change boring bar E.. SVLCL 95°, for indexable inserts VC., left-hand, Shank dia. DS / insert size: 8/05mm


Order data

Order number	268121 8/05
GTIN	4062406584177
Item class	21P

Technical description

Neck width L_4	6 mm
Shank $\varnothing D_s$	8 mm
ISO code toolholder	E08X SVLCR/L05
suitable indexable insert	VC.. 0501..
Overall length L	57 mm
Pack of insert screws	269028 26
Usable depth T	3 mm
Centre offset L_3	5 mm
Minimum pre-drill $\varnothing D_{min}$	9.2 mm
Head length L_1	26 mm
Setting angle κ	95 degrees
Insert size	5 mm
Standard	Works standard
Application type	left-hand
Tool material	Carbide
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 26	269028 26
------------------------------	-----------