

**Garant**

**Carbide boring bar E.. SVXCL 113°, for indexable inserts VC., left-hand, Shank Ø / insert size: 8/05mm**


**Order data**

Order number	261369 8/05
GTIN	4062406285883
Item class	21T

**Technical description**

Centre offset $L_3$	5 mm
Overall length $L$	80 mm
suitable indexable insert	VC.. 0501..
Minimum pre-drill $\varnothing D_{\min}$	9.2 mm
ISO code toolholder	E08F SVXCR/L05
Pack of insert screws	269028 27
Head length $L_1$	26 mm
Insert size	5 mm
Setting angle $\kappa$	113 degrees
Neck width $L_4$	6 mm
Clamping height $L_2$	7.5 mm
Usable depth $T$	3 mm
Shank $\varnothing D_s$	8 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	8xD

Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

---

## Accessories

Set of insert screws Type 26	269028 26
------------------------------	-----------