

Garant

Carbide boring bar E.. SV95CL 95°, for indexable inserts VC.., left-hand, Shank Ø / insert size: 8/05mm


Order data

Order number	261343 8/05
GTIN	4062406285869
Item class	21T

Technical description

suitable indexable insert	VC.. 0501..
Pack of insert screws	269028 27
Setting angle κ	95 degrees
ISO code toolholder	E08F SV95CR/L05
Clamping height L_2	7.5 mm
Neck width L_4	6 mm
Centre offset L_3	5 mm
Insert size	5 mm
Minimum pre-drill $\varnothing D_{\min}$	9.2 mm
Overall length L	80 mm
Head length L_1	26 mm
Usable depth T	3 mm
Shank $\varnothing D_s$	8 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	8×D

Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 26	269028 26
------------------------------	-----------