

Garant

**Clamping toolholder SDJCR 93°, for indexable inserts DC., right-hand,
Shank / insert size: 20/07mm**



Order data

Order number	260308 20/07
GTIN	4062406602246
Item class	21T

Technical description

Overall length L	125 mm
Head length L ₁	24 mm
ISO code toolholder	SDJCR/L 2020K07
Insert size	7 mm
Shank size	20 mm
suitable indexable insert	DC.. 0702..
Pack of insert screws	269028 22
Functional width L ₄	24 mm
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15