

Garant

**Clamping toolholder SDJCR 93°, for indexable inserts DC., right-hand,
Shank / insert size: 16/07mm**



Order data

Order number	260308 16/07
GTIN	4062406602239
Item class	21T

Technical description

Functional width L_4	20 mm
Head length L_1	22 mm
Shank size	16 mm
Pack of insert screws	269028 22
suitable indexable insert	DC.. 0702..
Overall length L	100 mm
ISO code toolholder	SDJCR/L 1616H11
Insert size	7 mm
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15