

Garant
Master Turn steel boring bar helical flutes A.. SVUCL, for indexable inserts VC., left-hand, Shank \varnothing / insert size: 25/16mm

Order data

Order number	261319 25/16
GTIN	4062406711146
Item class	21T

Technical description

suitable indexable insert	VC.. 1604..
Series	GARANT Master
Centre offset L_3	17 mm
Overall length L	200 mm
ISO code toolholder	A25R SVUCR/L16
Pack of insert screws	269028 8
Clamping height L_2	23 mm
Head length L_1	40 mm
Insert size	16 mm
Setting angle κ	93 degrees
Minimum pre-drill $\varnothing D_{\min}$	31 mm
Shank $\varnothing D_s$	25 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar