



Machine tap HSS-E, vaporised, M: M5



Order data

Order number	132645 M5
GTIN	4045197648884
Item class	12H

Description

Version:

Spiral point with oil grooves.

Guide section with oil grooves, but without chip flutes. Tolerance class: ISO 2 6H

Thread type: M

Tool material: HSS E

Standard: DIN 371

Tolerance class: ISO 2 6H

Thread pitch: 0.8 mm

Overall length L: 70 mm

Shank $\varnothing D_s$: 6 mm

Shank square \square : 4.9 mm

Tapping hole \varnothing : 4.2 mm

Technical description

Number of cutting edges Z	2
Thread pitch	0.8 mm
Number of clamping slots	2
Thread \varnothing	5 mm
Tapping hole \varnothing	4.2 mm
Standard	DIN 371
Shank $\varnothing D_s$	6 mm
Overall length L	70 mm
Shank square \square	4.9 mm

Tolerance class	ISO 2 6H
Tool material	HSS E
Thread depth	15 mm
Thread type	M
Thread size	M5
Coating	vaporised
Flank angle	60°
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	green
Type of product	Tap

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	11 m/min	N
Steel < 500 N/mm ²	suitable only under restricted conditions	12 m/min	P
Steel < 750 N/mm ²	suitable	8 m/min	P
Steel < 900 N/mm ²	suitable	7 m/min	P
Steel < 1100 N/mm ²	suitable only under restricted conditions	4 m/min	P
INOX < 900 N/mm ²	suitable	4 m/min	M
CuZn	suitable only under restricted conditions	12 m/min	N

Uni	suitable
Oil	suitable