


**Garant**
**Master Eco clamping toolholder short PCLNL 95°, for indexable inserts CN., left-hand, Shank / insert size: 16/12mm**

**Order data**

Order number	250001 16/12
GTIN	4062406733254
Item class	21U

**Description**
**Version:**

Highly efficient cooling directly on the cutter and additional flank face cooling.

**Note:**

Coolant transfer via slot on the underside of the shank in conjunction with GARANT Master Eco holder No. 319006 – 319136 or No. 317900 for shank length < 125 mm. Optional connection possibility via hose connection (G 1/8 inch) No. 269207 and 269208.

**Technical description**

Lever screw	259018 14
Overall length L	80 mm
suitable indexable insert	CN.. 1204..
Series	Master Eco
Insert size	12 mm
Lever	259015 15
Shim	259031 5
ISO code toolholder	PCLNR/L 1620F12
Shank size	16 mm

Spring	259046 4
Functional width L <sub>4</sub>	25 mm
Head length L <sub>1</sub>	30 mm
Standard	Works standard
Application type	left-hand
Through-coolant	yes
Setting angle $\kappa$	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar