

Garant
Master Eco clamping toolholder short PDJNR 93°, for indexable inserts DN., right-hand, Shank / insert size: 20/15mm

Order data

Order number	250624 20/15
GTIN	4062406728946
Item class	21U

Description
Version:

Highly efficient cooling directly on the cutter and additional flank face cooling.

Note:

Coolant transfer via slot on the underside of the shank in conjunction with GARANT Master Eco holders No. 319006 – 319136 or No. 317900 for shank length < 125 mm. Optional connection possibility via hose connection (G 1/8 inch) No. 269207 and 269208.

Technical description

Series	Master Eco
Head length L ₁	40 mm
Overall length L	100 mm
Functional width L ₄	25 mm
Insert size	15 mm
Lever	259015 17
Shim	259031 45
suitable indexable insert	DN.. 1506..
Lever screw	259018 17
Spring	259046 4

Shank size	20 mm
ISO code toolholder	PDJNR/L 2020H15
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	yes
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar