


Garant
Master Eco clamping toolholder short PSSNL 45°, for indexable inserts SN., left-hand, Shank / insert size: 25/12mm

Order data

Order number	251117 25/12
GTIN	4062406733858
Item class	21U

Description
Version:

Highly efficient cooling directly on the cutter and additional flank face cooling.

Note:

Coolant transfer via slot on the underside of the shank in conjunction with GARANT Master eco toolholders No. 319006 – 311936 or No. 317900 for shank length < 125 mm. Optional connection possibility via hose connection (G 1/8 inch) No. 269207 and 269208.

Technical description

Functional width L ₄	32 mm
ISO code toolholder	PSSNR/L 2525X12
suitable indexable insert	SN.. 1204..
Spring	259046 4
Overall length L	105 mm
Head length L ₁	35 mm
Series	Master Eco
Lever	259015 15
Shank size	25 mm

Shim	259031 46
Lever screw	259018 15
Insert size	12 mm
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	yes
Setting angle κ	45 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	QuickTurn clamping toolholder