

Garant
Master Eco clamping toolholder short MTJNR 93°, for indexable inserts TN., right-hand, Shank / insert size: 25/16mm

Order data

Order number	251404 25/16
GTIN	4062406734190
Item class	21U

Description
Version:

Highly efficient cooling directly on the cutter and additional flank face cooling.

Note:

Coolant transfer via slot on the underside of the shank in conjunction with GARANT Master Eco holders No. 319006 – 319136 or No. 317900 for shank length < 125 mm. Optional connection possibility via hose connection (G 1/8 inch) No. 269207 and 269208.

Technical description

Pin	259049 8
Functional width L ₄	32 mm
Shim	259033 9
Clamping claw	259038 20
Series	Master Eco
Shank size	25 mm
ISO code toolholder	MTJNR/L 2525X16
suitable indexable insert	TN.. 1604..
Head length L ₁	35 mm

Screw for clamping claw	259021 6
Overall length L	105 mm
Insert size	16 mm
Standard	Works standard
Application type	right-hand
Through-coolant	yes
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for hexagon, 1/4 inch E 6.3 Hexagon 3 mm	674242 3