

Garant
Die, UNF: 7/8-14


Order data

Order number	142620 7/8-14
GTIN	4045197084972
Item class	11K

Description

Version:

Closed, pre-slitted form; **with tapered lead chamfer on both sides** for easy start to the threading action and clean swarf evacuation in the direction of cutting. **1¾ turns lead chamfer.**

Application:

For UNF uniform fine threads ASME – B1.1.

Tolerance class: 2A
 Threads per inch: 14
 Thread Ø: 22.23 mm
 External Ø: 55 mm
 Height: 16 mm

Technical description

Thread Ø	22.23 mm
Height	16 mm
Threads per inch	14
External Ø	55 mm

Thread size	7/8-14 UNF
Cutting direction	right-hand
Thread type	UNF
Flank angle	60 °
Tool material	HSS
Standard	EN 22568
Tolerance class	2A
Type of product	Die

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions		
Steel < 500 N/mm ²	suitable		
Steel < 750 N/mm ²	suitable		
Oil	suitable		
dry	suitable only under restricted conditions		