


Garant
Master Eco clamping toolholder short MTJNL 93°, for indexable inserts TN., left-hand, Shank / insert size: 20/16mm

Order data

Order number	251405 20/16
GTIN	4062406734206
Item class	21U

Description
Version:

Highly efficient cooling directly on the cutter and additional flank face cooling.

Note:

Coolant transfer via slot on the underside of the shank in conjunction with GARANT Master Eco holders No. 319006 – 319136 or No. 317900 for shank length < 125 mm. Optional connection possibility via hose connection (G 1/8 inch) No. 269207 and 269208.

Technical description

Shank size	20 mm
Insert size	16 mm
Clamping claw	259038 20
Overall length L	95 mm
ISO code toolholder	MTJNR/L 2020X16
Functional width L ₄	25 mm
Head length L ₁	35 mm
suitable indexable insert	TN.. 1604..
Screw for clamping claw	259021 6

Shim	259033 9
Pin	259049 8
Series	Master Eco
Standard	Works standard
Application type	left-hand
Through-coolant	yes
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for hexagon, 1/4 inch E 6.3 Hexagon 3 mm	674242 3