

Garant**Indexable insert for turning VC.T 110304, for finish machining, Grade: HU7315-1**

Order data

Order number	261366 HU7315-1
GTIN	4062406381530
Item class	21G

Technical description

Cutting speed v_c main application	50 - 600 m/min
Cutting conditions	continuous
Tool material	Carbide
Cutting depth a_p	0.05 - 1.5 mm
Number of changes/inserts	2
Tolerance	G
Feed f	0.03 - 0.25 mm/rev.
ISO code indexable insert	VCGT 110304
Grade	HU7315-1
Main application	N

Chip breaker	AF
Coating	uncoated
Finishing/roughing assignment	Finishing
Corner radius	0.4 mm
Type of product	Indexable insert for turning