

**Garant****Toolholder with ratchet, All-steel, Overall length: 85mm****Order data**

Order number	148701 85
GTIN	4062406754631
Item class	11K

**Description****Version:**

With two-jaw chuck for clamping square shanks. Moveable T-handle with a groove centred and at each end for engaging the retaining ball. **Holder with stainless steel sheath**. Ratchet is reversible and can also be locked. **All-steel construction** for high torque applications. Clamping jaws milled and hardened for high toughness and optimum surface hardness.

**Application:**

Suitable for tapping holes where access is difficult.

**Note:**

The square sizes of other tap and reamer sizes can be found in the tables in the respective Product Groups.

**Technical description**

Overall length	85 mm
for hand taps DIN 352	M3 – M10
Capacity □	2.5 - 5.5 mm
Spare jaws No. 148712 size	85

Material	All-steel
Type of product	Pin vice