

Garant

Toolholder with ratchet long, All-steel, Overall length: 300mm



Order data

Order number	149001 300
GTIN	4062406754693
Item class	11K

Description

Version:

With two-jaw chuck for clamping square shanks. Moveable T-handle with a groove centred at each end for engaging the retaining ball. **Holder with stainless steel sheath**. Ratchet is reversible and can also be locked. **All-steel construction** for high torque applications. Clamping jaws milled and hardened for high toughness and optimum surface hardness.

Application:

Suitable for tapping holes where access is difficult.

Note:

The square sizes of other tap and reamer sizes can be found in the tables in the respective Product Groups.

Capacity □: 4.5 - 8 mm

for hand taps DIN 352: M5 – M12

Spare jaws No. 148712 size: 110

Technical description

Overall length	300 mm
for hand taps DIN 352	M5 – M12

Capacity <input type="checkbox"/>	4.5 - 8 mm
Spare jaws No. 148712 size	110
Material	All-steel
Type of product	Pin vice