

## Garant

**Jobber drill with stepped tip HSS-E Stainless steel, uncoated, Ø DC h8: 3mm**



### Order data

Order number	114008 3
GTIN	4062406866778
Item class	11Q

### Description

#### Version:

Chamfers are nitrided. Particularly sturdy and robust due to the **strengthened core diameter**. Ground flutes, with high concentricity. Precision ground point. Three **drive flats on the shank** for use in a 3-jaw chuck.

- **Ideal for producing precise holes in sheet metal, pipes, and profiles.**
- **Reliable spot drilling without centring or centre punching – even on curved surfaces – thanks to innovative ground point.**
- **Oblique drilling possible without any problems after the first level of the drill tip has penetrated the material.**
- **Drilling with significantly less force required than with conventional DIN338 HSS drills – up to a diameter of 13 mm directly in the cordless drill/driver.**
- **Stable and secure form fit in the 3-jaw chuck.**
- **General use across a wide spectrum of materials including plastic, wood and acrylic without tearing or splintering.**
- **The drill does not rattle or dig in – even in the case of thin-walled materials.**
- **Burr-free drill exit.**
- **Ideal for drilling out bolts and rivets.**

With special cutter geometry also for use in stainless steels.

#### Recommendation:

#### Maximum drilling depth:

$$L_2 = L_C - 1.5 \times D_C$$

#### Note:

Drills with plain shank, **without drive flat**.

### Technical description

Point angle	118°
-------------	------

Nominal $\varnothing D_c$	3 mm
Overall length L	61 mm
Shank $\varnothing D_s$	3 mm
Standard	DIN 338
Flute length $L_c$	33 mm
recommended maximum drilling depth $L_2$	28.5 mm
Number of cutting edges Z	2
Feed f in steel < 750 N/mm <sup>2</sup>	0.06 mm/rev.
Tolerance nominal $\varnothing$	h8
Shank	Plain shank
Coating	uncoated
Tool material	HSS E
Type	INOX
Through-coolant	no
Colour ring	blue
Type of product	Jobber drill

## User data

	Suitability	$V_c$	ISO code
Alu plastics	suitable only under restricted conditions		
Aluminium (short chipping)	suitable only under restricted conditions		
Alu > 10% Si	suitable only under restricted conditions		
Steel < 500 N/mm <sup>2</sup>	suitable		
Steel < 750 N/mm <sup>2</sup>	suitable		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1100 N/mm <sup>2</sup>	suitable only under restricted conditions		

INOX < 900 N/mm <sup>2</sup>	suitable		
INOX > 900 N/mm <sup>2</sup>	suitable		
GG(G)	suitable	30 m/min	K
CuZn	suitable		
Oil	suitable		
wet maximum	suitable		