

Garant
Master Turn steel boring bar helical flutes A.. SCLCR 95°, for indexable inserts CC., right-hand, Shank Ø / insert size: 10/06mm

Order data

| | |
|--------------|---------------|
| Order number | 260030 10/06 |
| GTIN | 4062406575748 |
| Item class | 21T |

Technical description

| | |
|-------------------------------|-------------------------------|
| Minimum pre-drill Ø D_{min} | 12 mm |
| suitable indexable insert | CC.. 0602.. |
| Centre offset L_3 | 6 mm |
| Shank Ø D_s | 10 mm |
| Series | GARANT Master |
| Pack of insert screws | 269028 7 |
| Overall length L | 125 mm |
| ISO code toolholder | A10K SCLCR/L06 |
| Insert size | 6 mm |
| Head length L_1 | 20 mm |
| Clamping height L_2 | 9 mm |
| Standard | DIN 8024 |
| Application type | right-hand |
| Boring depth up to | 3×D |
| Through-coolant | yes |
| Application | Internal longitudinal turning |

Type of product

Boring Bar