

**Garant**

**Carbide quick-change boring bar E.. SVLCR 95°, for indexable inserts VC.., right-hand, Shank dia. DS / insert size: 8/05mm**


**Order data**

Order number	268122 8/05
GTIN	4062406584184
Item class	21P

**Technical description**

Head length $L_1$	26 mm
Pack of insert screws	269028 26
Minimum pre-drill $\varnothing D_{\min}$	9.2 mm
Overall length L	57 mm
Neck width $L_4$	6 mm
Usable depth T	3 mm
Shank $\varnothing D_s$	8 mm
Setting angle $\kappa$	95 degrees
suitable indexable insert	VC.. 0501..
Centre offset $L_3$	5 mm
Insert size	5 mm
ISO code toolholder	E08X SV95CR/L05
Standard	Works standard
Application type	right-hand
Tool material	Carbide
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

---

## Accessories

Set of insert screws Type 26	269028 26
------------------------------	-----------