

Garant

Clamping toolholder SDJCL 93°, for indexable inserts DC., left-hand, Shank / insert size: 20/07mm



Order data

Order number	260309 20/07
GTIN	4062406602260
Item class	21T

Technical description

Pack of insert screws	269028 22
Head length L ₁	24 mm
Shank size	20 mm
Insert size	7 mm
Functional width L ₄	24 mm
suitable indexable insert	DC.. 0702..
ISO code toolholder	SDJCR/L 2020K11
Overall length L	125 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15