

Garant
GARANT Master Mute boring bar, left-hand, Shank \varnothing / insert size: 40/09mm

Order data

Order number	260045 40/09
GTIN	4067263623427
Item class	29E

Description
Version:

Round shank without clamping face.

Note:

Do not clamp on the area marked S!

Technical description

suitable indexable insert	CC.. 09T3..
Series	Master Mute
Centre offset L_3	27 mm
Minimum pre-drill $\varnothing D_{\min}$	50 mm
Shank $\varnothing D_s$	40 mm
Setting angle κ	95 degrees
ISO code toolholder	A40X SCLCR/L09
Insert size	9 mm
Pack of insert screws	269028 50
Overhang L_1	200 mm
Overall length L	343 mm
non-clamping range S	240 mm
Standard	DIN 8024
Application type	left-hand

Vibration	damped
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar