

Garant

**Carbide boring bar E... SVOCR, for indexable inserts VC., right-hand, Shank
Ø / insert size: 8/05mm**



Order data

Order number	261376 8/05
GTIN	4062406710835
Item class	21T

Technical description

Minimum pre-drill $\varnothing D_{\min}$	8 mm
Setting angle κ	140 degrees
suitable indexable insert	VC.. 0501..
Insert size	5 mm
Centre offset L_3	3 mm
Clamping height L_2	7.5 mm
Head length L_1	26 mm
Pack of insert screws	269028 26
ISO code toolholder	E08F SVOCR/L05
Overall length L	80 mm
Shank $\varnothing D_s$	8 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar