



HOLEX Pro Tap machine tap HSS-E, TiN, M: M2,5



Order data

Order number	132680 M2,5
GTIN	4062406719937
Item class	12I

Description

Version:

With spiral point.

Guide section with oil grooves, but without chip flutes.

HOLEX Pro Tap general-purpose tap.

Sturdy design suitable for a wide spectrum of materials.

Improved HSS-E tool material with low-friction TiN coating. Tolerance class: ISO 2 6H

Thread type: M

Tool material: HSS E

Standard: DIN 371

Tolerance class: ISO 2 6H

Thread pitch: 0.45 mm

Overall length L: 50 mm

Shank $\varnothing D_s$: 2.8 mm

Shank square \square : 2.1 mm

Tapping hole \varnothing : 2.05 mm

Technical description

Shank $\varnothing D_s$	2.8 mm
Thread pitch	0.45 mm
Thread type	M
Tolerance class	ISO 2 6H
Number of cutting edges Z	3
Thread depth	7.5 mm

Overall length L	50 mm
Thread Ø	2.5 mm
Standard	DIN 371
Number of clamping slots	3
Shank square □	2.1 mm
Tapping hole Ø	2.05 mm
Tool material	HSS E
Thread size	M2.5
Coating	TiN
Flank angle	60°
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	green
Type of product	Tap

User data

	Suitability	V _c	ISO code
Alu plastics	suitable	24 m/min	N
Aluminium (short chipping)	suitable	25 m/min	N
Alu > 10% Si	suitable	10 m/min	N
Steel < 500 N/mm ²	suitable	24 m/min	P
Steel < 750 N/mm ²	suitable	20 m/min	P
Steel < 900 N/mm ²	suitable	15 m/min	P

Steel < 1100 N/mm ²	suitable only under restricted conditions	8 m/min	P
INOX < 900 N/mm ²	suitable	8 m/min	M
CuZn	suitable only under restricted conditions	15 m/min	N
Uni	suitable		
Oil	suitable		
wet maximum	suitable		