

Garant
for indexable inserts SD.. SDJC 93°, right-hand, Shank / insert size: 20/11mm


Order data

Order number	260290 20/11
GTIN	4067263122425
Item class	21U

Description

Version:

Highly efficient cooling directly on the cutting edge and additional flank face cooling.

Note:

Coolant transfer via slot on the underside of the shank in conjunction with GARANT Master Eco holder No. 319006 – 311936 or No. 317900 for shank length < 125 mm. Optional connection possibility via hose connection (G 1/8 inch) No. 269207 and 269208.

Technical description

Insert size	11 mm
Functional width L ₄	25 mm
Shim screw	269013 7
Head length L ₁	30 mm
Shank size	20 mm
Pack of insert screws	269023 3
Shim	269007 1
Series	Master Eco
suitable indexable insert	DC.. 11T3..
Overall length L	90 mm
ISO code toolholder	SDJCR/L 2020X11

Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	yes
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Screw-on toolholder