

**Garant**
**Clamping toolholder SCLCL 95°, for indexable inserts SC., left-hand, Shank / insert size: 16/09mm**

**Order data**

Order number	260027 16/09
GTIN	4067263122395
Item class	21U

**Description**
**Version:**

Highly efficient cooling directly on the cutting edge and additional flank face cooling.

**Note:**

Coolant transfer via slot on the underside of the shank in conjunction with GARANT Master Eco toolholders No. 319006 – 311936 or No. 317900 for shank length < 125 mm. Optional connection possibility via hose connection (G 1/8 inch) No. 269207 and 269208.

**Technical description**

Overall length L	80 mm
Functional width L <sub>4</sub>	20 mm
ISO code toolholder	SCLCR/L 1616F09
Head length L <sub>1</sub>	30 mm
Insert size	9 mm
Pack of insert screws	269028 28
Shank size	16 mm
suitable indexable insert	CC.. 09T3..
Series	Master Eco
Standard	DIN ISO 5610

Application type	left-hand
Through-coolant	yes
Setting angle $\kappa$	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Screw-on toolholder