

Garant
Master Eco clamping toolholder short PCLNR 95°, for indexable inserts CN., right-hand, Shank / insert size: 25/12mm

Order data

Order number	250000 25/12
GTIN	4062406733247
Item class	21U

Description
Version:

Highly efficient cooling directly on the cutter and additional flank face cooling.

Note:

Coolant transfer via slot on the underside of the shank in conjunction with GARANT Master Eco holder No. 319006 – 319136 or No. 317900 for shank length < 125 mm. Optional connection possibility via hose connection (G 1/8 inch) No. 269207 and 269208.

Technical description

Functional width L ₄	32 mm
Insert size	12 mm
Spring	259046 4
Shank size	25 mm
Shim	259031 5
Series	Master Eco
Head length L ₁	30 mm
Lever screw	259018 15
Overall length L	100 mm

suitable indexable insert	CN.. 1204..
Lever	259015 15
ISO code toolholder	PCLNR/L 2525H12
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	yes
Setting angle κ	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar