


Garant
for indexable inserts SD.. SDJC 93°, left-hand, Shank / insert size: 25/11mm


Order data

Order number	260291 25/11
GTIN	4067263122463
Item class	21U

Description

Version:

Highly efficient cooling directly on the cutting edge and additional flank face cooling.

Note:

Coolant transfer via slot on the underside of the shank in conjunction with GARANT Master Eco holder No. 319006 – 311936 or No. 317900 for shank length < 125 mm. Optional connection possibility via hose connection (G 1/8 inch) No. 269207 and 269208.

Technical description

Shank size	25 mm
Shim	269007 1
ISO code toolholder	SDJCR/ L 2525H11
Overall length L	100 mm
Shim screw	269013 7
Series	Master Eco
Insert size	11 mm
suitable indexable insert	DC.. 11T3..
Head length L ₁	30 mm
Pack of insert screws	269023 3

Functional width L ₄	32 mm
Standard	Works standard
Application type	left-hand
Through-coolant	yes
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Screw-on toolholder