

Garant
**Eco clamping toolholder SVJB 93°, for indexable inserts SV.., right-hand,
Shank / insert size: 25/16mm**

Order data

Order number	261122 25/16
GTIN	4067263122555
Item class	21U

Description
Version:

Highly efficient cooling directly on the cutting edge and additional flank face cooling.

Note:

Coolant transfer via slot on the underside of the shank in conjunction with GARANT Master Eco holders No. 319006 – 319136 or No. 317900 for shank length < 125 mm. Optional connection possibility via hose connection (G 1/8 inch) No. 269207 and 269208.

Technical description

Insert size	16 mm
Head length L ₁	40 mm
Shank size	25 mm
Functional width L ₄	32 mm
Shim	259033 5
Series	Master Eco
Pack of insert screws	269023 3
ISO code toolholder	SVJBR/L 2525X16
suitable indexable insert	VB.. 1604..

Overall length L	110 mm
Shim screw	269013 7
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	yes
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Screw-on toolholder