

Garant
Master Eco clamping toolholder short PDJNL 93°, for indexable inserts DN., left-hand, Shank / insert size: 16/11mm

Order data

Order number	250625 16/11
GTIN	4062406728960
Item class	21U

Description
Version:

Highly efficient cooling directly on the cutter and additional flank face cooling.

Note:

Coolant transfer via slot on the underside of the shank in conjunction with GARANT Master Eco holders No. 319006 – 319136 or No. 317900 for shank length < 125 mm. Optional connection possibility via hose connection (G 1/8 inch) No. 269207 and 269208.

Technical description

Lever screw	259018 16
Shim	259031 44
Series	Master Eco
Insert size	11 mm
Head length L ₁	35 mm
Shank size	16 mm
suitable indexable insert	DN.. 1104..
Lever	259015 16
Functional width L ₄	20 mm
ISO code toolholder	PDJNR/L 1616X11

Overall length L	85 mm
Spring	259046 5
Standard	Works standard
Application type	left-hand
Through-coolant	yes
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar