

Garant
Master Eco clamping toolholder short PWLNR 95°, for indexable inserts WN., right-hand, Shank / insert size: 16/08mm

Order data

Order number	251910 16/08
GTIN	4062406733872
Item class	21U

Description
Version:

Highly efficient cooling directly on the cutter and additional flank face cooling.

Note:

Coolant transfer via slot on the underside of the shank in conjunction with GARANT Master Eco holders No. 319006 – 319136 or No. 317900 for shank length < 125 mm. Optional connection possibility via hose connection (G 1/8 inch) No. 269207 and 269208.

Technical description

ISO code toolholder	PWLNR/L 1620F08
Shank size	16 mm
Overall length L	80 mm
Lever	259015 15
Shim	259031 48
Insert size	8 mm
suitable indexable insert	WN.. 0804..
Functional width L ₄	25 mm
Head length L ₁	30 mm

Lever screw	259018 15
Series	Master Eco
Spring	259046 4
Standard	Works standard
Application type	right-hand
Through-coolant	yes
Setting angle κ	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	QuickTurn clamping toolholder