

**Garant**

**Master Eco clamping toolholder short PWLNR 95°, for indexable inserts WN., right-hand, Shank / insert size: 20/06mm**



## Order data

Order number	251910 20/06
GTIN	4062406733889
Item class	21U

## Description

### Version:

Highly efficient cooling directly on the cutter and additional flank face cooling.

### Note:

Coolant transfer via slot on the underside of the shank in conjunction with GARANT Master Eco holders No. 319006 – 319136 or No. 317900 for shank length < 125 mm. Optional connection possibility via hose connection (G 1/8 inch) No. 269207 and 269208.

## Technical description

Shank size	20 mm
Lever screw	259018 16
Spring	259046 5
Overall length L	90 mm
Lever	259015 16
suitable indexable insert	WN.. 0604..
Insert size	6 mm
Series	Master Eco
ISO code toolholder	PWLNR/L 2020X06

Functional width $L_4$	25 mm
Head length $L_1$	30 mm
Shim	259031 47
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	yes
Setting angle $\kappa$	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	QuickTurn clamping toolholder