

**Garant**
**Master Eco clamping toolholder short PWLNL 95°, for indexable inserts WN., left-hand, Shank / insert size: 25/06mm**

**Order data**

Order number	251911 25/06
GTIN	4062406734169
Item class	21U

**Description**
**Version:**

Highly efficient cooling directly on the cutter and additional flank face cooling.

**Note:**

Coolant transfer via slot on the underside of the shank in conjunction with GARANT Master Eco holders No. 319006 – 319136 or No. 317900 for shank length < 125 mm. Optional connection possibility via hose connection (G 1/8 inch) No. 269207 and 269208.

**Technical description**

Shim	259031 47
ISO code toolholder	PWLNR/L 2525H06
Lever	259015 16
Series	Master Eco
Head length L <sub>1</sub>	30 mm
Insert size	6 mm
Shank size	25 mm
Functional width L <sub>4</sub>	32 mm
Lever screw	259018 16

Spring	259046 5
suitable indexable insert	WN.. 0604..
Overall length L	100 mm
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	yes
Setting angle $\kappa$	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar