


Garant
Master Eco clamping toolholder short PWLNL 95°, for indexable inserts WN., left-hand, Shank / insert size: 25/08mm

Order data

Order number	251911 25/08
GTIN	4062406734176
Item class	21U

Description
Version:

Highly efficient cooling directly on the cutter and additional flank face cooling.

Note:

Coolant transfer via slot on the underside of the shank in conjunction with GARANT Master Eco holders No. 319006 – 319136 or No. 317900 for shank length < 125 mm. Optional connection possibility via hose connection (G 1/8 inch) No. 269207 and 269208.

Technical description

Head length L ₁	30 mm
Lever screw	259018 15
Shank size	25 mm
suitable indexable insert	WN.. 0804..
Insert size	8 mm
Lever	259015 15
ISO code toolholder	PWLNLR/L 2525H08
Series	Master Eco
Functional width L ₄	32 mm

Spring	259046 4
Shim	259031 48
Overall length L	100 mm
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	yes
Setting angle κ	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar