

Garant
Master Eco clamping toolholder short PWLNL 95°, for indexable inserts WN., left-hand, Shank / insert size: 20/06mm

Order data

Order number	251911 20/06
GTIN	4062406734145
Item class	21U

Description
Version:

Highly efficient cooling directly on the cutter and additional flank face cooling.

Note:

Coolant transfer via slot on the underside of the shank in conjunction with GARANT Master Eco holders No. 319006 – 319136 or No. 317900 for shank length < 125 mm. Optional connection possibility via hose connection (G 1/8 inch) No. 269207 and 269208.

Technical description

Lever	259015 16
Functional width L ₄	25 mm
Insert size	6 mm
Overall length L	90 mm
ISO code toolholder	PWLNLR/L 2020X06
Series	Master Eco
Spring	259046 5
Shank size	20 mm
Shim	259031 47

Lever screw	259018 16
Head length L ₁	30 mm
suitable indexable insert	WN.. 0604..
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	yes
Setting angle κ	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar