

Garant
Master Eco clamping toolholder short MWLNR 95°, for indexable inserts WN.., right-hand, Shank / insert size: 20/08mm

Order data

Order number	251922 20/08
GTIN	4062406734664
Item class	21U

Description
Version:

Highly efficient cooling directly on the cutter and additional flank face cooling.

Note:

Coolant transfer via slot on the underside of the shank in conjunction with GARANT Master Eco holders No. 319006 – 319136 or No. 317900 for shank length < 125 mm. Optional connection possibility via hose connection (G 1/8 inch) No. 269207 and 269208.

Technical description

Pin	259049 7
Series	Master Eco
Shim	259033 6
Clamping claw	259038 18
Head length L ₁	35 mm
Functional width L ₄	25 mm
Screw for clamping claw	259021 6
suitable indexable insert	WN.. 0804..
Shank size	20 mm

Insert size	8 mm
ISO code toolholder	MWLNR/L 2020X08
Overall length L	95 mm
Standard	Works standard
Application type	right-hand
Through-coolant	yes
Setting angle κ	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	QuickTurn clamping toolholder