

**Garant**
**Toolholder with ratchet, All-steel, Overall length: 117mm**

**Order data**

Order number	148701 117
GTIN	4062406754655
Item class	11K

**Description**
**Version:**

With two-jaw chuck for clamping square shanks. Moveable T-handle with a groove centred at each end for engaging the retaining ball. **Holder with stainless steel sheath**. Ratchet is reversible and can also be locked. **All-steel construction** for high torque applications. Clamping jaws milled and hardened for high toughness and optimum surface hardness. **Heavy-duty version** for taps up to M20.

**With** head-side **hexagon** with 22 mm jaw width.

**Application:**

Suitable for tapping holes where access is difficult.

**Note:**

The square sizes of other tap and reamer sizes can be found in the tables in the respective Product Groups.

Capacity □: 8.5 - 12.5 mm

for hand taps DIN 352: M13 – M20

Spare jaws No. 148712 size: 117

**Technical description**

Capacity □	8.5 - 12.5 mm
Overall length	110 mm
for hand taps DIN 352	M13 – M20
Spare jaws No. 148712 size	117
Material	All-steel

Type of product

Pin vice