


**Garant**

**Indexable insert for turning ZCMX 10T304, for "4 in 1" turning and boring tools, Grade: HBZ140**

**Order data**

Order number	268433 HBZ140
GTIN	4062406770136
Item class	21K

**Description****Version:**

General-purpose medium grit substrate with PVD coating. First choice for turning and drilling applications.

**Technical description**

Finishing/roughing assignment	Finishing
Feed rate $f$ when drilling	0.03 - 0.12 mm
Number of changes/inserts	2
Cutting depth $a_p$	0.4 - 2 mm
Tool material	Carbide
ISO code indexable insert	ZCMX 10T304
Feed rate $f$ when turning	0.1 - 0.3 mm
Grade	HBZ140

Corner radius	0.4 mm
Cutting conditions	slightly interrupted
Cutting speed $v_c$ main application	50 - 190 m/min
Main application	M
suitable for tool dia. $D_c$	20 mm
Type of product	Indexable insert for turning