

Garant

Indexable insert for turning ZCMX 10T304, for "4 in 1" turning and boring tools, Grade: HBZ035

**Order data**

Order number	268433 HBZ035
GTIN	4062406770112
Item class	21K

Description**Version:**

General-purpose medium grit substrate with PVD coating. First choice for turning and drilling applications.

Technical description

Grade	HBZ035
Cutting depth a_p	0.4 - 2 mm
Tool material	Carbide
Cutting speed v_c main application	50 - 190 m/min
Cutting conditions	slightly interrupted
Feed rate f when turning	0.1 - 0.3 mm
Corner radius	0.4 mm
Main application	P

Finishing/roughing assignment	Finishing
Number of changes/inserts	2
ISO code indexable insert	ZCMX 10T304
Feed rate f when drilling suitable for tool dia. D_c	0.03 - 0.12 mm
Type of product	20 mm
	Indexable insert for turning