


Garant**Centring vice basic device Xtric, Type: 125XSA****Order data**

Order number	363000 125XSA
GTIN	4067263098799
Item class	310

Description**Version:**

- **Very good accessibility and perfectly symmetrical.**
- **Fully hardened and precision milled on the underside.**
- **Clamps raw materials and finished parts with the least possible backstroke of the jaws / component.**
- **Central alignment delivers perfectly centred clamping.**
- **The clamping range can be changed by reversing the jaws.**

Application:

Perfect for 5-face machining. Centred clamping.

Suitable for:

Top jaws No. 363010 – 363045.

Supplied with:

Base body, spindle, spindle nuts and four clamping studs suitable for automation extension base No. 360164 XP80Z.

Optional extras:

Torque wrench No. 656050, socket No. 642229 13, assembly station No. 358595 80.

Note:

Suitable for the GARANT TurnTable automation system in combination with / for automation extension base No. 360164 XP80Z. Suitable top jaws No. 363010 – 363045 are not included in the scope of supply. Clamping situation S2 arises by reversing the jaws.

Technical description

Weight	10.6 kg
maximum clamping force	32 kN
Width across flats	13 mm
Width across flats	5 mm
B	120 mm
L	186 mm
maximum torque	132 Nm
Version	Zero-point clamping system
Height H	54 mm
Reference dimension	80 mm
Colour code	Xtric 125
Type of product	Machine vice