

Garant

Indexable insert for turning CC.T 09T302, for medium machining, Grade: HB7310

**Order data**

| | |
|--------------|---------------|
| Order number | 260148 HB7310 |
| GTIN | 4045197667885 |
| Item class | 21G |

Technical description

| | |
|--------------------------------------|--------------------|
| Cutting speed v_c main application | 350 - 600 m/min |
| Chip breaker | AM |
| Cutting depth a_p | 0.1 - 4 mm |
| Feed f | 0.05 - 0.5 mm/rev. |
| Cutting conditions | continuous |
| Main application | N |
| Corner radius | 0.2 mm |
| Grade | HB7310 |
| Finishing/roughing assignment | Finishing |
| Finishing/roughing assignment | Finishing |

| | |
|-------------------------------|------------------------------|
| Finishing/roughing assignment | Finishing |
| Tool material | Carbide |
| ISO code indexable insert | CCGT 09T302 |
| Number of changes/inserts | 2 |
| Tolerance | G |
| Type of product | Indexable insert for turning |