

Garant**Indexable insert for turning CC.T 09T308, for medium machining, Grade: HU7310**

Order data

Order number	260152 HU7310
GTIN	4045197668219
Item class	21G

Technical description

Corner radius	0.8 mm
Cutting depth a_p	0.1 - 4 mm
Main application	N
Cutting speed v_c main application	350 - 600 m/min
Chip breaker	AM
Cutting conditions	continuous
Feed f	0.05 - 0.5 mm/rev.
Grade	HU7310
Finishing/roughing assignment	Finishing
Tool material	Carbide

Coating	uncoated
ISO code indexable insert	CCMT 09T308
Number of changes/inserts	2
Tolerance	G
Type of product	Indexable insert for turning