

Garant

**Clamping toolholder CKJNR 93°, for indexable inserts KNUX., right-hand,
Shank / insert size: 20/16mm**



Order data

Order number	251008 20/16
GTIN	4045197650665
Item class	21T

Technical description

Functional width L ₄	30 mm
Shim	259031 4
Shim pins pack	259044 3
ISO code toolholder	CKJNR/L 2020K16
Head length L ₁	32 mm
Insert size	16 mm
Spring	259046 3
Screw for clamp	259021 3
Shank size	20 mm
suitable indexable insert	KNUX 1604.. R/L
Clamp	259038 16
Overall length L	125 mm
Standard	Works standard
Application type	right-hand
Through-coolant	no

Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Screw for clamping claw Type 3	259021 3
Shim Type 4	259031 4
Clamping claw Type 16	259038 16
Set of shim pins 10 pieces Type 3	259044 3
Spring Type 3	259046 3
8 mm blade with magnet with 1/4 inch bit holder overall length 50 mm	659874 50
Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm	659906 1600
Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm	659957 1600
Precision Bit for hexagon, 1/4 inch E 6.3 Hexagon 4 mm	674242 4