

**Garant**
**Clamping toolholder, right-hand, Shank / insert size: 25/08mm**

**Order data**

Order number	251912 25/08
GTIN	4045197651266
Item class	21T

**Description**

Clamping toolholder 25/08 mm ISO code toolholder: MWLNR/L 2525M08  
 suitable indexable insert: WN.. 0804..  
 Functional width L<sub>4</sub>: 32 mm  
 Head length L<sub>1</sub>: 31 mm  
 Overall length L: 150 mm  
 Screw set: 259023 2

**Technical description**

Functional width L <sub>4</sub>	32 mm
Pin	259049 2
Shim	259031 41
suitable indexable insert	WN.. 0804..
Screw set	259023 2
Head length L <sub>1</sub>	31 mm
Shank size	25 mm
Clamping claw	259038 12
ISO code toolholder	MWLNR/L 2525M08
Insert size	8 mm
Overall length L	150 mm

Series	QuickTurn
Application type	right-hand
Standard	DIN ISO 5610
Through-coolant	no
Setting angle $\kappa$	95°
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

## Accessories

PrecisionBit for hexagon, 1/4 inch E 6.3 Hexagon 3 mm	674242 3
Shim	259580
Shim Type 41	259031 41
Pin	259600
Set of screws 10 pieces	259620
Pin Type 2	259049 2
Clamping claw	259560
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
Set of screws 10 pieces Type 2	259023 2
Clamping claw Type 12	259038 12