

Garant

**Carbide boring bar E.. SDQCL 107,5°, for indexable inserts DC., left-hand,
Shank Ø / insert size: 8/07mm**


Order data

Order number	260321 8/07
GTIN	4067263622710
Item class	21T

Technical description

Centre offset L_3	7 mm
Shank Ø D_s	8 mm
Setting angle κ	107.5 degrees
ISO code toolholder	E08K SDQCR/L07
Overall length L	125 mm
Minimum pre-drill Ø D_{min}	12 mm
Clamping height L_2	7.6 mm
Overhang L_1	29 mm
suitable indexable insert	DC.. 0702..
Pack of insert screws	269028 7
Insert size	7 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8